

Overland Storage / Tandberg Data

Software Compatibility Matrix

EFFECTIVE: April 2016

Software Compatibility Matrix

EFFECTIVE: April 2016
P/N: 1021900



Software Compatibility Matrix

EFFECTIVE: April 2016



Purpose of this document

The purpose of this document is to assist in deploying compatible hardware and software solutions. The information contained within this document assumes:

- All related hardware components have the most up to date firmware version
- Each third-party backup application is up to date with the most current build and available patches
- Operating systems are up to date with the latest build, patches and/or service pack(s)

Limitations of this document:

Overland Storage and Tandberg Data provide technical support for in warranty hardware related issues only
Overland Storage and Tandberg Data does not provide technical support for third-party software.
This document does not contain information related to all builds or sub-versions of a particular operating system.
For all other questions or problems we recommend that you contact the software vendor for assistance

About Overland Storage and Tandberg Data

Overland Storage is a global provider of unified data management and data protection solutions across the data lifecycle. Tandberg Data is a wholly owned subsidiary of Overland Storage and a global leader in data storage and protection solutions for SMBs, remote offices and workgroups. By providing an integrated range of technologies and services for primary, nearline, offline, and archival data storage, Overland and Tandberg Data make it easy and cost effective to manage different tiers of information over time, whether distributed data is across the hall or across the globe.

©2014 Overland Storage and Tandberg Data, a wholly owned subsidiary of Overland Storage, Inc. All trademarks and registered trademarks are the property of their respective owners. The information contained herein is subject to change without notice and is provided "as is" without warranty of any kind. Neither Overland Storage nor Tandberg Data shall be liable for technical or editorial errors or omissions contained herein. Specifications subject to change without notice.

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	Drive Inquiry String	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux - Red Hat	Linux - SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Acronis	Backup & Recovery	11.5	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Archware	P5	5.1	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ARCserve	ARCserve	r16.5	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓					Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	ASG	Time Navigator	4.3	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	Barracuda	Yosemite Backup	10.3	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓				Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓						✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	CommVault	Simpana	10.0	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Overland Storage	CommVault	Simpana	10.0	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓					✓	✓		✓	✓		Overland Storage
Overland Storage	CommVault	Simpana	10.0	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓		✓					✓	✓		✓	✓	✓	Overland Storage
Overland Storage	CommVault	Simpana	11.0	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓					✓	✓		✓	✓		Overland Storage
Overland Storage	CommVault	Simpana	11.0	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓		✓					✓	✓		✓	✓	✓	Overland Storage
Tape Drives - LTO	EMC	NetWorker	8.2	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓					✓	✓	✓	✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓		✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	EMC	NetWorker	8.2	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓					✓	✓		✓	✓	✓	Tandberg Data

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	Drive Inquiry String	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux - Red Hat	Linux - SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
Tape Drives - LTO	HP	Data Protector	8.1	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓		✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓		✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓		✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓		✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓		✓	Tandberg Data
Tape Drives - LTO	HP	Data Protector	8.1	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓		✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	IBM	Tivoli Storage Manager	7.1	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Microsoft	Data Protection Manager	2012	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓							Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Quest	NetVault	10.0	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓		✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	Retrospect	Retrospect	9.0	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	SEP	Sesam	4.2	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓		✓	✓	✓	Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2014	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓											Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓													Tandberg Data

Software Compatibility Matrix - Tape Drives

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	Drive Inquiry String	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux - Red Hat	Linux - SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓													Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	2012	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓													Tandberg Data
Overland Storage	Symantec	Backup Exec	15	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7		✓	✓	✓	✓	✓										Overland Storage
Overland Storage	Symantec	Backup Exec	15	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓	✓										Overland Storage
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	NetBackup	7.6	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Overland Storage	Symantec	NetBackup	7.6	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓	✓				✓	✓		✓	✓		Overland Storage
Overland Storage	Symantec	NetBackup	7.6	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6				✓	✓	✓				✓	✓		✓	✓		Overland Storage
Overland Storage	Symantec	NetBackup	7.7	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓	✓				✓	✓		✓	✓		Overland Storage
Overland Storage	Symantec	NetBackup	7.7	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6				✓	✓	✓				✓	✓		✓	✓		Overland Storage
Tape Drives - LTO	Symantec	Backup Exec	15	LTO2	HH	SAS	TANDBERGLTO-2*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO2	HH	SCSI	TANDBERGLTO-2*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO3	HH	SAS	TANDBERGLTO-3*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO3	HH	SCSI	TANDBERGLTO-3*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO5	HH	FC	TANDBERGLTO-5*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO6	HH	FC	TANDBERGLTO-6*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Symantec	Backup Exec	15	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓ ¹	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO2	HH	SAS	TANDBERGLTO-2*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO2	HH	SCSI	TANDBERGLTO-2*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO3	HH	SAS	TANDBERGLTO-3*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO3	HH	SCSI	TANDBERGLTO-3*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO4	HH	SAS	TANDBERGLTO-4*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO4	HH	SCSI	TANDBERGLTO-4*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO5	HH	FC	TANDBERGLTO-5*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO5	HH	SAS	TANDBERGLTO-5*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO6	HH	FC	TANDBERGLTO-6*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Tolis	BRU	2.0	LTO6	HH	SAS	TANDBERGLTO-6*HH									✓	✓	✓		✓			Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	7.0	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	7.0	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	7.0	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	7.0	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	7.0	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	7.0	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	8	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	8	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	8	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	8	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Veeam	Backup & Replication	8	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Virtos	SOS Backup	6.6	LTO4	HH	SAS	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Virtos	SOS Backup	6.6	LTO4	HH	SCSI	TANDBERGLTO-4*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Virtos	SOS Backup	6.6	LTO5	HH	FC	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Virtos	SOS Backup	6.6	LTO5	HH	SAS	TANDBERGLTO-5*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Virtos	SOS Backup	6.6	LTO6	HH	FC	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Virtos	SOS Backup	6.6	LTO6	HH	SAS	TANDBERGLTO-6*HH	✓	✓	✓	✓	✓	✓										Tandberg Data
Tape Drives - LTO	Xendata	Workstation	6.1	LTO5	HH	FC	TANDBERGLTO-5*HH							✓									Tandberg Data
Tape Drives - LTO	Xendata	Workstation	6.1	LTO5	HH	SAS	TANDBERGLTO-5*HH							✓									Tandberg Data
Tape Drives - LTO	Xendata	Workstation	6.1	LTO6	HH	FC	TANDBERGLTO-6*HH							✓									Tandberg Data
Tape Drives - LTO	Xendata	Workstation	6.1	LTO6	HH	SAS	TANDBERGLTO-6*HH							✓									Tandberg Data
Tape Drives - LTO	Xendata	Server	7.0	LTO4	HH	FC	TANDBERGLTO-4*HH		✓	✓													Tandberg Data
Tape Drives - LTO	Xendata	Server	7.0	LTO4	HH	SAS	TANDBERGLTO-4*HH		✓	✓													Tandberg Data
Tape Drives - LTO	Xendata	Server	7.0	LTO5	HH	FC	TANDBERGLTO-5*HH		✓	✓													Tandberg Data
Tape Drives - LTO	Xendata	Server	7.0	LTO5	HH	SAS	TANDBERGLTO-5*HH		✓	✓													Tandberg Data
Tape Drives - LTO	Xendata	Server	7.0	LTO6	HH	FC	TANDBERGLTO-6*HH		✓	✓													Tandberg Data
Tape Drives - LTO	Xendata	Server	7.0	LTO6	HH	SAS	TANDBERGLTO-6*HH		✓	✓													Tandberg Data

Notes:

1) BackupExec 15 Media Server can only be installed on Windows Server 2003 R2 64bit Edition

EFFECTIVE: April 2016

Page 6 of 36

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	DriveInquiryString	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux Red Hat	Linux SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
NEOs StorageLoader	Archware	P5	5.1	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOs StorageLoader	Archware	P5	5.1	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5		✓	✓	✓	✓				✓							Overland Storage
NEOs StorageLoader	Archware	P5	5.1	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	Archware	P5	5.3	LTO7	HH	FC	IBM~~~~~ULTRIUM-TD7				✓	✓				✓							Overland Storage
NEO 8000e	Archware	P5	5.3	LTO7	HH	SAS	IBM~~~~~ULTRIUM-TD7				✓	✓				✓							Overland Storage
NEOxl 60	Archware	P5	5.3	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOxl 60	Archware	P5	5.3	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOxl 80	Archware	P5	5.3	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOxl 80	Archware	P5	5.3	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOs T48	Archware	P5	5.3	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOs T48	Archware	P5	5.3	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOs T24	Archware	P5	5.3	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOs T24	Archware	P5	5.3	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOs StorageLoader	Archware	P5	5.3	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEOs StorageLoader	Archware	P5	5.3	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓				✓							Overland Storage
NEO 100s	Archware	P5	5.1	LTO4	HH	SAS	IBM~~~~~ULTRIUM-HH4		✓	✓	✓	✓				✓	✓	✓		✓			Overland Storage
NEO 100s	Archware	P5	5.1	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5		✓	✓	✓	✓				✓	✓	✓		✓			Overland Storage
NEO 100s	ARCserve	ARCserve	16.5	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 100s	ARCserve	ARCserve	16.5	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 100s	ARCserve	ARCserve	16.5	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEO 200s/400s	ARCserve	ARCserve	16.5	LTO-4	HH	SCSI	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 200s/400s	ARCserve	ARCserve	16.5	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 200s/400s	ARCserve	ARCserve	16.5	LTO-4	HH	FC	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 200s/400s	ARCserve	ARCserve	16.5	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 200s/400s	ARCserve	ARCserve	16.5	LTO-5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 200s/400s	ARCserve	ARCserve	16.5	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEO 200s/400s	ARCserve	ARCserve	16.5	LTO-6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEO 2000e/4000e	ARCserve	ARCserve	16.5	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 2000e/4000e	ARCserve	ARCserve	16.5	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 2000e/4000e	ARCserve	ARCserve	16.5	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 2000e/4000e	ARCserve	ARCserve	16.5	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 2000e/4000e	ARCserve	ARCserve	16.5	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 2000e/4000e	ARCserve	ARCserve	16.5	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓				✓							Overland Storage
NEO 2000e/4000e	ARCserve	ARCserve	16.5	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	ARCserve	ARCserve	16.5	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	ARCserve	ARCserve	16.5	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	ARCserve	ARCserve	16.5	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	ARCserve	ARCserve	16.5	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	ARCserve	ARCserve	16.5	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	ARCserve	ARCserve	16.5	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓				✓							Overland Storage
NEO 8000e	ARCserve	ARCserve	16.5	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓				✓							Overland Storage
NEOxl 60	ARCserve	ARCserve	16.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOxl 80	ARCserve	ARCserve	16.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOs T48	ARCserve	ARCserve	16.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOs T24	ARCserve	ARCserve	16.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOxl 60	ARCserve	ARCserve	16.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEOxl 80	ARCserve	ARCserve	16.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEOs T48	ARCserve	ARCserve	16.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOs T48	ARCserve	ARCserve	16.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOs T24	ARCserve	ARCserve	16.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓							Overland Storage
NEOxl 60	ARCserve	ARCserve	16.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5		✓	✓	✓	✓				✓							Overland Storage
NEOxl 80	ARCserve	ARCserve	16.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5		✓	✓	✓	✓				✓							Overland Storage
NEOs T48	ARCserve	ARCserve	16.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEOs T48	ARCserve	ARCserve	16.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEOs T24	ARCserve	ARCserve	16.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEOs StorageLoader	ARCserve	ARCserve	16.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEOs StorageLoader	ARCserve	ARCserve	16.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6	✓	✓	✓	✓	✓				✓							Overland Storage
NEOs StorageLoader	ARCserve	ARCserve	16.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓							Overland Storage
NEOs StorageLoader	ARCserve	ARCserve	16.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6	✓	✓	✓	✓	✓				✓							Overland Storage
StorageLoader LTO	ARCserve	ARCserve	16.5	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLoader LTO	ARCserve	ARCserve	16.5	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLoader LTO	ARCserve	ARCserve	16.5	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLoader LTO	ARCserve	ARCserve	16.5	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLoader LTO	ARCserve	ARCserve	16.5	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLibrary T24	ARCserve	ARCserve	16.5	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLibrary T24	ARCserve	ARCserve	16.5	LTO4	HH	SCSI	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLibrary T24	ARCserve	ARCserve	16.5	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLibrary T24	ARCserve	ARCserve	16.5	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLibrary T24	ARCserve	ARCserve	16.5	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLibrary T24	ARCserve	ARCserve	16.5	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data
StorageLibrary T24	ARCserve	ARCserve	16.5	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓									Tandberg Data

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	DriveInquiryString	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux Red Hat	Linux SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
StorageLibrary T40+	ARCServe	ARCServe	16.5	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T40+	ARCServe	ARCServe	16.5	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T40+	ARCServe	ARCServe	16.5	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T40+	ARCServe	ARCServe	16.5	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T40+	ARCServe	ARCServe	16.5	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T80+	ARCServe	ARCServe	16.5	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T80+	ARCServe	ARCServe	16.5	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T80+	ARCServe	ARCServe	16.5	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T80+	ARCServe	ARCServe	16.5	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T80+	ARCServe	ARCServe	16.5	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T80+	ARCServe	ARCServe	16.5	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T120+	ARCServe	ARCServe	16.5	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓	✓					✓					Tandberg Data
StorageLibrary T120+	ARCServe	ARCServe	16.5	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓	✓					✓					Tandberg Data
StorageLibrary T120+	ARCServe	ARCServe	16.5	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓					✓					Tandberg Data
StorageLibrary T120+	ARCServe	ARCServe	16.5	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓					✓					Tandberg Data
StorageLibrary T120+	ARCServe	ARCServe	16.5	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓					✓					Tandberg Data
StorageLibrary T120+	ARCServe	ARCServe	16.5	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓					✓					Tandberg Data
StorageLibrary T160+	ARCServe	ARCServe	16.5	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T160+	ARCServe	ARCServe	16.5	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T160+	ARCServe	ARCServe	16.5	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T160+	ARCServe	ARCServe	16.5	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T160+	ARCServe	ARCServe	16.5	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
StorageLibrary T160+	ARCServe	ARCServe	16.5	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓	✓										Tandberg Data
NEO 100s	Arkeia	Network Backup	10.0	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓	✓			✓	✓	✓		✓	✓	✓	Overland Storage
NEO 100s	Arkeia	Network Backup	10.0	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓	✓			✓	✓	✓		✓	✓	✓	

EFFECTIVE: April 2016



Overland Storage and Tandberg Data

EFFECTIVE: April 2016



Overland Storage and Tandberg Data Tape Automation Page 10

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	DriveInquiryString	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux Red Hat	Linux SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
StorageLibrary T24	CommVault	Simpana	10.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	CommVault	Simpana	10.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	CommVault	Simpana	10.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	CommVault	Simpana	10.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	CommVault	Simpana	10.0	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	CommVault	Simpana	10.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	CommVault	Simpana	10.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	CommVault	Simpana	10.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	CommVault	Simpana	10.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T80+	CommVault	Simpana	10.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T80+	CommVault	Simpana	10.0	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T80+	CommVault	Simpana	10.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T80+	CommVault	Simpana	10.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T80+	CommVault	Simpana	10.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T80+	CommVault	Simpana	10.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T120+	CommVault	Simpana	10.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T120+	CommVault	Simpana	10.0	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T120+	CommVault	Simpana	10.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T120+	CommVault	Simpana	10.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T120+	CommVault	Simpana	10.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T120+	CommVault	Simpana	10.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T160+	CommVault	Simpana	10.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓	✓	Tandberg Data
StorageLibrary T160+	CommVault	Simpana	10.0	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T160+	CommVault	Simpana	10.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T160+	CommVault	Simpana	10.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T160+	CommVault	Simpana	10.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
StorageLibrary T160+	CommVault	Simpana	10.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓				✓		✓	✓	✓	✓		Tandberg Data
NEOXl 60	Commvault	Simpana	10.0	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 80	Commvault	Simpana	10.0	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T48	Commvault	Simpana	10.0	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T24	Commvault	Simpana	10.0	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 60	Commvault	Simpana	10.0	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 80	Commvault	Simpana	10.0	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T48	Commvault	Simpana	10.0	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T24	Commvault	Simpana	10.0	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 60	Commvault	Simpana	10.0	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 80	Commvault	Simpana	10.0	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T48	Commvault	Simpana	10.0	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T24	Commvault	Simpana	10.0	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 60	Commvault	Simpana	10.0	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 80	Commvault	Simpana	10.0	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T48	Commvault	Simpana	10.0	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs T24	Commvault	Simpana	10.0	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs StorageLoader	Commvault	Simpana	10.0	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs StorageLoader	Commvault	Simpana	10.0	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs StorageLoader	Commvault	Simpana	10.0	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOs StorageLoader	Commvault	Simpana	10.0	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEOXl 60	Commvault	Simpana	10.0	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOXl 80	Commvault	Simpana	10.0	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOs T48	Commvault	Simpana	10.0	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOs T24	Commvault	Simpana	10.0	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOXl 60	Commvault	Simpana	10.0	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOXl 80	Commvault	Simpana	10.0	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOs T48	Commvault	Simpana	10.0	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOs T24	Commvault	Simpana	10.0	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOs StorageLoader	Commvault	Simpana	10.0	LTO7	HH	FC	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEOs StorageLoader	Commvault	Simpana	10.0	LTO7	HH	SAS	IBM~~~~~ULTRIUM-HH7				✓	✓						✓		✓	✓		Overland Storage
NEO 8000e	Commvault	Simpana	11.0	LTO7	FH	FC	IBM~~~~~ULTRIUM-TD7				✓	✓						✓		✓	✓		Overland Storage
NEO 100s	Commvault	Simpana	10.0	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 100s	Commvault	Simpana	10.0	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 100s	Commvault	Simpana	10.0	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 200s/400s	Commvault	Simpana	10.0	LTO-4	HH	SCSI	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 200s/400s	Commvault	Simpana	10.0	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 200s/400s	Commvault	Simpana	10.0	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 200s/400s	Commvault	Simpana	10.0	LTO-5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 200s/400s	Commvault	Simpana	10.0	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 200s/400s	Commvault	Simpana	10.0	LTO-6	HH	FC	IBM~~~~~ULTRIUM-HH6	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 2000e/4000e	Commvault	Simpana	10.0	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 2000e/4000e	Commvault	Simpana	10.0	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 2000e/4000e	Commvault	Simpana	10.0	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 2000e/4000e	Commvault	Simpana	10.0	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage
NEO 2000e/4000e	Commvault	Simpana	10.0	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓				✓		✓		✓	✓		Overland Storage

EFFECTIVE: April 2016

Overland Storage and Tandberg Data

overland
storage

TANDBERG DATA

TANDBERG DATA 

Overland Storage and Tandberg Data Tape Automation Page 13

EFFECTIVE: April 2016



Overland Storage and Tandberg Data

EFFECTIVE: April 2016



Overland Storage and Tandberg Data

TANDBERG DATA

Overland Storage and Tandberg Data Tape Automation Page 16

EFFECTIVE: April 2016



Overland Storage and Tandberg Data

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	DriveInquiryString	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux Red Hat	Linux SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
NEO 200s/400s	Oracle	Secure Backup	10.4	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 200s/400s	Oracle	Secure Backup	10.4	LTO-4	HH	FC	IBM~~~~~ULTRIUM-HH4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 200s/400s	Oracle	Secure Backup	10.4	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 200s/400s	Oracle	Secure Backup	10.4	LTO-5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 200s/400s	Oracle	Secure Backup	10.4	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 200s/400s	Oracle	Secure Backup	10.4	LTO-6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6		✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6		✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 2000e/4000e	Oracle	Secure Backup	10.4	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6		✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 8000e	Oracle	Secure Backup	10.4	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 8000e	Oracle	Secure Backup	10.4	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 8000e	Oracle	Secure Backup	10.4	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 8000e	Oracle	Secure Backup	10.4	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 8000e	Oracle	Secure Backup	10.4	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5	✓	✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 8000e	Oracle	Secure Backup	10.4	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6		✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 8000e	Oracle	Secure Backup	10.4	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6		✓	✓							✓	✓		✓	✓	✓	Overland Storage
NEO 100s	Retrospect	Retrospect	9.0	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓				✓							Overland Storage
NEO 100s	Retrospect	Retrospect	9.0	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 100s	Retrospect	Retrospect	9.0	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓					✓						Overland Storage
NEO 200s/400s	Retrospect	Retrospect	9.0	LTO-4	HH	SCSI	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 200s/400s	Retrospect	Retrospect	9.0	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 200s/400s	Retrospect	Retrospect	9.0	LTO-4	HH	FC	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 200s/400s	Retrospect	Retrospect	9.0	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 200s/400s	Retrospect	Retrospect	9.0	LTO-5	HH	FC	IBM~~~~~ULTRIUM-HH5	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 200s/400s	Retrospect	Retrospect	9.0	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓					✓						Overland Storage
NEO 200s/400s	Retrospect	Retrospect	9.0	LTO-6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓					✓						Overland Storage
NEO 2000e/4000e	Retrospect	Retrospect	9.0	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 2000e/4000e	Retrospect	Retrospect	9.0	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 2000e/4000e	Retrospect	Retrospect	9.0	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 2000e/4000e	Retrospect	Retrospect	9.0	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 2000e/4000e	Retrospect	Retrospect	9.0	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 2000e/4000e	Retrospect	Retrospect	9.0	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓					✓						Overland Storage
NEO 2000e/4000e	Retrospect	Retrospect	9.0	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓					✓						Overland Storage
NEO 8000e	Retrospect	Retrospect	9.0	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 8000e	Retrospect	Retrospect	9.0	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 8000e	Retrospect	Retrospect	9.0	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 8000e	Retrospect	Retrospect	9.0	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 8000e	Retrospect	Retrospect	9.0	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5	✓	✓	✓	✓	✓					✓						Overland Storage
NEO 8000e	Retrospect	Retrospect	9.0	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓					✓						Overland Storage
NEO 8000e	Retrospect	Retrospect	9.0	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6		✓	✓	✓	✓					✓						Overland Storage
StorageLoader LTO	Retrospect	Retrospect	9.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLoader LTO	Retrospect	Retrospect	9.0	LTO4	HH	SCSI	Hp~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLoader LTO	Retrospect	Retrospect	9.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLoader LTO	Retrospect	Retrospect	9.0	LTO5	HH	SAS	Hp~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLoader LTO	Retrospect	Retrospect	9.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO4	HH	SCSI	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T24	Retrospect	Retrospect	9.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T40+	Retrospect	Retrospect	9.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T40+	Retrospect	Retrospect	9.0	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T40+	Retrospect	Retrospect	9.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T40+	Retrospect	Retrospect	9.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T40+	Retrospect	Retrospect	9.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T40+	Retrospect	Retrospect	9.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T80+	Retrospect	Retrospect	9.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T80+	Retrospect	Retrospect	9.0	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T80+	Retrospect	Retrospect	9.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T80+	Retrospect	Retrospect	9.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T80+	Retrospect	Retrospect	9.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T80+	Retrospect	Retrospect	9.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T120+	Retrospect	Retrospect	9.0	LTO4	HH	SAS	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T120+	Retrospect	Retrospect	9.0	LTO4	HH	SCSI	HP~~~~~Ultrium*4-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T120+	Retrospect	Retrospect	9.0	LTO5	HH	SAS	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T120+	Retrospect	Retrospect	9.0	LTO5	HH	FC	HP~~~~~Ultrium*5-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T120+	Retrospect	Retrospect	9.0	LTO6	HH	SAS	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data
StorageLibrary T120+	Retrospect	Retrospect	9.0	LTO6	HH	FC	HP~~~~~Ultrium*6-SCSI	✓	✓	✓	✓	✓		✓		✓							Tandberg Data

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	DriveInquiryString	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux Red Hat	Linux SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
StorageLibrary T160+	Retrospect	Retrospect	9.0	LTO4	HH	SAS	HP~~~~~Ultrim®4-SCSI	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
StorageLibrary T160+	Retrospect	Retrospect	9.0	LTO4	HH	SCSI	HP~~~~~Ultrim®4-SCSI	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
StorageLibrary T160+	Retrospect	Retrospect	9.0	LTO5	HH	SAS	HP~~~~~Ultrim®5-SCSI	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
StorageLibrary T160+	Retrospect	Retrospect	9.0	LTO5	HH	FC	HP~~~~~Ultrim®5-SCSI	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
StorageLibrary T160+	Retrospect	Retrospect	9.0	LTO6	HH	SAS	HP~~~~~Ultrim®6-SCSI	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
StorageLibrary T160+	Retrospect	Retrospect	9.0	LTO6	HH	FC	HP~~~~~Ultrim®6-SCSI	✓	✓	✓	✓	✓	✓	✓	✓								Tandberg Data
NEOxl 60	Retrospect	Retrospect	12.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6									✓							Overland Storage
NEOxl 80	Retrospect	Retrospect	12.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6									✓							Overland Storage
NEOs T48	Retrospect	Retrospect	12.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6									✓							Overland Storage
NEOs T24	Retrospect	Retrospect	12.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6									✓							Overland Storage
NEOxl 60	Retrospect	Retrospect	12.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH6									✓							Overland Storage
NEOxl 60	Retrospect	Retrospect	12.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOxl 80	Retrospect	Retrospect	12.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOs T48	Retrospect	Retrospect	12.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOs T24	Retrospect	Retrospect	12.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOxl 80	Retrospect	Retrospect	12.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOs T48	Retrospect	Retrospect	12.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOs T24	Retrospect	Retrospect	12.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	12.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	12.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6									✓							Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	12.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5									✓							Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	12.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6									✓							Overland Storage
NEO 8000e	Retrospect	Retrospect	12.5	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5									✓							Overland Storage
NEO 8000e	Retrospect	Retrospect	12.5	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5									✓							Overland Storage
NEO 8000e	Retrospect	Retrospect	12.5	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6									✓							Overland Storage
NEO 8000e	Retrospect	Retrospect	12.5	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6									✓							Overland Storage
NEOxl 60	Retrospect	Retrospect	10.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOxl 80	Retrospect	Retrospect	10.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOs T48	Retrospect	Retrospect	10.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOs T24	Retrospect	Retrospect	10.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOxl 60	Retrospect	Retrospect	10.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOxl 80	Retrospect	Retrospect	10.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOs T48	Retrospect	Retrospect	10.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOs T24	Retrospect	Retrospect	10.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOxl 60	Retrospect	Retrospect	10.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOxl 80	Retrospect	Retrospect	10.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOs T48	Retrospect	Retrospect	10.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOs T24	Retrospect	Retrospect	10.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOxl 60	Retrospect	Retrospect	10.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOxl 80	Retrospect	Retrospect	10.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOs T48	Retrospect	Retrospect	10.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOs T24	Retrospect	Retrospect	10.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	10.5	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	10.5	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	10.5	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5			✓		✓		✓									Overland Storage
NEOs StorageLoader	Retrospect	Retrospect	10.5	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6			✓		✓		✓									Overland Storage
NEO 8000e	Retrospect	Retrospect	10.5	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5			✓		✓		✓									Overland Storage
NEO 8000e	Retrospect	Retrospect	10.5	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5			✓		✓		✓									Overland Storage
NEO 8000e	Retrospect	Retrospect	10.5	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6			✓		✓		✓									Overland Storage
NEO 8000e	Retrospect	Retrospect	10.5	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6			✓		✓		✓									Overland Storage
StorageLoader LTO	SEP	Sesam	4.2	LTO4	HH	SAS	HP~~~~~Ultrim®4-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓		✓	✓	✓		Tandberg Data
StorageLoader LTO	SEP	Sesam	4.2	LTO4	HH	SCSI	HP~~~~~Ultrim®4-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLoader LTO	SEP	Sesam	4.2	LTO5	HH	FC	HP~~~~~Ultrim®5-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLoader LTO	SEP	Sesam	4.2	LTO5	HH	SAS	HP~~~~~Ultrim®5-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLoader LTO	SEP	Sesam	4.2	LTO6	HH	SAS	HP~~~~~Ultrim®6-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	SEP	Sesam	4.2	LTO4	HH	SAS	HP~~~~~Ultrim®4-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	SEP	Sesam	4.2	LTO4	HH	SCSI	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	SEP	Sesam	4.2	LTO5	HH	SAS	HP~~~~~Ultrim®5-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	SEP	Sesam	4.2	LTO5	HH	FC	HP~~~~~Ultrim®5-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	SEP	Sesam	4.2	LTO6	HH	SAS	HP~~~~~Ultrim®6-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T24	SEP	Sesam	4.2	LTO6	HH	FC	HP~~~~~Ultrim®6-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	SEP	Sesam	4.2	LTO4	HH	SAS	HP~~~~~Ultrim®4-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data
StorageLibrary T40+	SEP	Sesam	4.2	LTO4	HH	SCSI	HP~~~~~Ultrim®4-SCSI	✓	✓	✓	✓	✓		✓	✓	✓	✓	✓	✓	✓	✓		Tandberg Data

TANDBERG DATA

Overland Storage and Tandberg Data

EFFECTIVE: April 2016



Overland Storage and Tandberg Data

TANDBERG DATA Overland Storage and Tandberg Data Tape Automation Page 22

EFFECTIVE: April 2016



Overland Storage and Tandberg Data

EFFECTIVE: April 2016



Overland Storage and Tandberg Data

TANDBERG DATA

Overland Storage and Tandberg Data Tape Automation Page 25 of 36

TANDBERG DATA Overland Storage and Tandberg Data Tape Automation Page 26

Software Compatibility Matrix - Tape Automation

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	DriveInquiryString	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux Red Hat	Linux SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
NEOs T24	Veeam	Backup & Replication	8	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5		✓	✓	✓	✓											Overland Storage
NEOs StorageLoader	Veeam	Backup & Replication	8	LTO5	HH	SAS	IBM~~~~~ULTRIUM-HH5		✓	✓	✓	✓											Overland Storage
NEOs StorageLoader	Veeam	Backup & Replication	8	LTO6	HH	SAS	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓											Overland Storage
NEOs StorageLoader	Veeam	Backup & Replication	8	LTO5	HH	FC	IBM~~~~~ULTRIUM-HH5		✓	✓	✓	✓											Overland Storage
NEOs StorageLoader	Veeam	Backup & Replication	8	LTO6	HH	FC	IBM~~~~~ULTRIUM-HH6		✓	✓	✓	✓											Overland Storage
StorageLoader LTO	Virto	SOS Backup	6.6	LTO4	HH	SAS	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLoader LTO	Virto	SOS Backup	6.6	LTO4	HH	SCSI	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLoader LTO	Virto	SOS Backup	6.6	LTO5	HH	SAS	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLoader LTO	Virto	SOS Backup	6.6	LTO5	HH	SCSI	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLoader LTO	Virto	SOS Backup	6.6	LTO6	HH	SAS	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T24	Virto	SOS Backup	6.6	LTO4	HH	SAS	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T24	Virto	SOS Backup	6.6	LTO4	HH	SCSI	IBM~~~~~ULTRIUM-HH4	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T24	Virto	SOS Backup	6.6	LTO5	HH	SAS	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T24	Virto	SOS Backup	6.6	LTO5	HH	FC	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T24	Virto	SOS Backup	6.6	LTO6	HH	SAS	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T24	Virto	SOS Backup	6.6	LTO6	HH	FC	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T40+	Virto	SOS Backup	6.6	LTO4	HH	SAS	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T40+	Virto	SOS Backup	6.6	LTO4	HH	SCSI	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T40+	Virto	SOS Backup	6.6	LTO5	HH	SAS	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T40+	Virto	SOS Backup	6.6	LTO5	HH	FC	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T40+	Virto	SOS Backup	6.6	LTO6	HH	SAS	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T40+	Virto	SOS Backup	6.6	LTO6	HH	FC	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T80+	Virto	SOS Backup	6.6	LTO4	HH	SAS	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T80+	Virto	SOS Backup	6.6	LTO4	HH	SCSI	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T80+	Virto	SOS Backup	6.6	LTO5	HH	SAS	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T80+	Virto	SOS Backup	6.6	LTO5	HH	FC	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T80+	Virto	SOS Backup	6.6	LTO6	HH	SAS	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T80+	Virto	SOS Backup	6.6	LTO6	HH	FC	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T120+	Virto	SOS Backup	6.6	LTO4	HH	SAS	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T120+	Virto	SOS Backup	6.6	LTO4	HH	SCSI	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T120+	Virto	SOS Backup	6.6	LTO5	HH	SAS	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T120+	Virto	SOS Backup	6.6	LTO5	HH	FC	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T120+	Virto	SOS Backup	6.6	LTO6	HH	SAS	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T120+	Virto	SOS Backup	6.6	LTO6	HH	FC	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T120+	Virto	SOS Backup	6.6	LTO4	HH	SAS	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T160+	Virto	SOS Backup	6.6	LTO4	HH	SCSI	HP~~~~~Ultrium^4-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T160+	Virto	SOS Backup	6.6	LTO5	HH	SAS	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T160+	Virto	SOS Backup	6.6	LTO5	HH	FC	HP~~~~~Ultrium^5-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T160+	Virto	SOS Backup	6.6	LTO6	HH	SAS	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
StorageLibrary T160+	Virto	SOS Backup	6.6	LTO6	HH	FC	HP~~~~~Ultrium^6-SCSI	✓	✓	✓	✓	✓											Tandberg Data
NEO 200s/400s	Xendata	Server	6.01	LTO-4	HH	SCSI	IBM~~~~~ULTRIUM-HH4			✓													Overland Storage
NEO 200s/400s	Xendata	Server	6.01	LTO-4	HH	SAS	IBM~~~~~ULTRIUM-HH4			✓													Overland Storage
NEO 200s/400s	Xendata	Server	6.01	LTO-4	HH	FC	IBM~~~~~ULTRIUM-HH4			✓													Overland Storage
NEO 200s/400s	Xendata	Server	6.01	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5			✓													Overland Storage
NEO 200s/400s	Xendata	Server	6.01	LTO-5	HH	FC	IBM~~~~~ULTRIUM-HH5			✓													Overland Storage
NEO 200s/400s	Xendata	Server	6.01	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6			✓													Overland Storage
NEO 200s/400s	Xendata	Server	6.01	LTO-6	HH	FC	IBM~~~~~ULTRIUM-HH6			✓													Overland Storage
NEO 2000e/4000e	Xendata	Server	6.01	LTO-4	FH	SCSI	IBM~~~~~ULTRIUM-TD4			✓													Overland Storage
NEO 2000e/4000e	Xendata	Server	6.01	LTO-4	FH	SAS	IBM~~~~~ULTRIUM-TD4			✓													Overland Storage
NEO 2000e/4000e	Xendata	Server	6.01	LTO-4	FH	FC	IBM~~~~~ULTRIUM-TD4			✓													Overland Storage
NEO 2000e/4000e	Xendata	Server	6.01	LTO-5	FH	SAS	IBM~~~~~ULTRIUM-TD5			✓													Overland Storage
NEO 2000e/4000e	Xendata	Server	6.01	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5			✓													Overland Storage
NEO 2000e/4000e	Xendata	Server	6.01	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6			✓													Overland Storage
NEO 2000e/4000e	Xendata	Server	6.01	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6			✓													Overland Storage
NEO 8000e	Xendata	Server	6.01	LTO-5	FH	FC	IBM~~~~~ULTRIUM-TD5			✓													Overland Storage
NEO 8000e	Xendata	Server	6.01	LTO-6	FH	SAS	IBM~~~~~ULTRIUM-TD6			✓													Overland Storage
NEO 8000e	Xendata	Server	6.01	LTO-6	FH	FC	IBM~~~~~ULTRIUM-TD6			✓													Overland Storage

Notes:

1) BackupExec 15 Media Server can only be installed on Windows Server 2003 R2 64bit Edition

Software Compatibility Matrix - Linear Tape File System - Tape Drives

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	Drive Inquiry String	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	MacOSX	Linux Red Hat	Linux SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
OVRL LTO-5 HH	IBM	LTFS-SDE	2.2.1.0	LTO-5	HH	SAS	IBM~~~~~ULTRIUM-HH5			✓	✓	✓		✓	✓	✓	✓	✓					Overland Storage
OVRL LTO 6 HH	IBM	LTFS-SDE	2.2.1.0	LTO-6	HH	SAS	IBM~~~~~ULTRIUM-HH6			✓	✓	✓		✓	✓	✓	✓	✓					Overland Storage
OVRL LTO-5 HH	TAD	SOS	2.2.1	LTO-5	HH	SAS	HP~~~~~Ultrium^5-SCSI		✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
OVRL LTO-5 HH	TAD	SOS	2.2.1	LTO-5	HH	FC	HP~~~~~Ultrium^5-SCSI		✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
OVRL LTO 6 HH	TAD	SOS	2.2.1	LTO-6	HH	SAS	HP~~~~~Ultrium^6-SCSI		✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data
OVRL LTO 6 HH	TAD	SOS	2.2.1	LTO-5	HH	FC	HP~~~~~Ultrium^6-SCSI		✓	✓	✓	✓		✓	✓	✓	✓	✓					Tandberg Data

- Notes
- 1) Administrator access is required to run SOS with Windows 8 & 8.1
 - 2) LTFS currently does not support P212 and P222 controllers on Windows 32 bit systems.
 - 3) RHEL 6 update 1 through update 5
 - 4) RHEL 5 update 5 through update 10
 - 5) SLES 11 SP2
 - 6) Minimum Mac version supported is Mac 10.7 (LTFS requires OSXFUSE 2.5.1 for Mac 10.7 and 10.8 and OSXFUSE 2.6.2 for Mac 10.9)
 - 7) LTFS Standalone software for Windows is not compatible with systems that have Apple iTunes installed. This is due to a filter driver installed as part of iTunes, which prevents correct control of the tape device.

TANDBERG DATA Overland Storage and Tandberg Data LTFS Automation Page 29 of 36

Software Compatibility Matrix - RDX

EFFECTIVE: April 2016



Product	Software Vendor	Software	Version	Drive Type	HH/FH	Interface	Drive Inquiry String	Windows 2003	Windows 2008	Windows 2008 R2	Windows 2012	Windows 2012 R2	Windows Vista	Windows 7 Pro	Windows 8	Windows 10	MacOSX	Linux - Red Hat	Linux - SUSE	NetWare	Solaris	AIX	HP-UX	Vendor
RDX QuikStor	Acronis	Backup & Recovery	11.5	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓ ³					Tandberg Data
RDX QuikStor	Acronis	Backup & Recovery	11.5	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓ ⁴					Tandberg Data
RDX QuikStor	Archware	P5	5.1	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓ ³		✓			Tandberg Data
RDX QuikStor	Archware	P5	5.1	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓		✓			Tandberg Data
RDX QuikStor	ASG	Time Navigator	4.3	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓ ³					Tandberg Data
RDX QuikStor	ASG	Time Navigator	4.3	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓		✓	✓	✓	Tandberg Data
RDX QuikStor	Barracuda	Yosemite Backup	10.3	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓		✓			Tandberg Data
RDX QuikStor	Barracuda	Yosemite Backup	10.3	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓		✓			Tandberg Data
RDX QuikStor	Quest	NetVault	10.0	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓ ³		✓	✓	✓	Tandberg Data
RDX QuikStor	Quest	NetVault	10.0	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓		✓	✓	✓	Tandberg Data
RDX QuikStor	Barracuda	Yosemite Backup	10.3	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓ ³	✓				Tandberg Data
RDX QuikStor	Barracuda	Yosemite Backup	10.3	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓	✓				Tandberg Data
RDX QuikStor	CommVault	Simpna	10.0	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓ ³		✓	✓	✓	Tandberg Data
RDX QuikStor	CommVault	Simpna	10.0	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓		✓	✓	✓	Tandberg Data
RDX QuikStor	ARCserve	ARCserve	16.5	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	ARCserve	ARCserve	16.5	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	EMC	NetWorker	8.2	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓ ³		✓	✓	✓	Tandberg Data
RDX QuikStor	EMC	NetWorker	8.2	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓		✓	✓	✓	Tandberg Data
RDX QuikStor	HP	Data Protector	8.1	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓ ³		✓		✓	Tandberg Data
RDX QuikStor	HP	Data Protector	8.1	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓			✓	✓		✓		✓	Tandberg Data
RDX QuikStor	Microsoft	Data Protection Manager	2012	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Microsoft	Window Native Backup	N/A	RDX	HH	USB3	TANDBERGGRDX	✓ ^{1,4,5}	✓ ^{4,5}	✓ ^{2,4,5}	✓ ^{3,4,5}	✓ ^{3,4,5}	✓	✓	✓									Tandberg Data
RDX QuikStor	Open Source	TAR	N/A	RDX	HH	SATA	TANDBERGGRDX											✓	✓					Tandberg Data
RDX QuikStor	Open Source	TAR	N/A	RDX	HH	USB	TANDBERGGRDX											✓	✓					Tandberg Data
RDX QuikStor	Paragon	Hard Disk Manager	14	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Paragon	Hard Disk Manager	14	RDX	HH	USB	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Paragon	Protect & Restore	3.2	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Paragon	Protect & Restore	3.2	RDX	HH	USB	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Retrospect	Retrospect	9.0	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓							Tandberg Data
RDX QuikStor	Retrospect	Retrospect	9.0	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓							Tandberg Data
RDX QuikStor	SEP	Sesam	4.2	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓ ³		✓	✓	✓	Tandberg Data
RDX QuikStor	SEP	Sesam	4.2	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓		✓	✓	✓		✓	✓	✓	Tandberg Data
RDX QuikStor	Symantec	Backup Exec	15	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Symantec	Backup Exec	15	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Symantec	Backup Exec	2014	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Symantec	Backup Exec	2014	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Symantec	Backup Exec	2012	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Symantec	Backup Exec	2012	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Symantec	System Recovery Desktop	2013	RDX	HH	SATA	TANDBERGGRDX						✓	✓	✓	✓ ³								Tandberg Data
RDX QuikStor	Symantec	System Recovery Desktop	2013	RDX	HH	USB3	TANDBERGGRDX						✓	✓	✓	✓ ³								Tandberg Data
RDX QuikStor	Symantec	System Recovery Server	2013	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Symantec	System Recovery Server	2013	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Tandberg Data	AccuGuard	8	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Tandberg Data	AccuGuard	8	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Tandberg Data	AccuGuard	9	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Tandberg Data	AccuGuard	9	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Veeam	Backup & Replication	7.0	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Veeam	Backup & Replication	7.0	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Veeam	Backup & Replication	8	RDX	HH	SATA	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Veeam	Backup & Replication	8	RDX	HH	USB3	TANDBERGGRDX	✓	✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Veeam	Endpoint Backup	1	RDX	HH	SATA	TANDBERGGRDX		✓	✓	✓	✓	✓	✓	✓									Tandberg Data
RDX QuikStor	Veeam	Endpoint Backup	1	RDX	HH	USB3	TANDBERGGRDX		✓	✓	✓	✓	✓	✓	✓									Tandberg Data

Notes:

- 1) A hotfix is available from Microsoft that allows NT Backup on Windows Server 2003 to support spanning across RDX cartridges. See Microsoft KB article 932059.
- 2) Microsoft Windows Server 2008 R2 native backup utility has the following limitations: scheduled image backup is not supported, individual file restore is not supported and partial system backup is not supported.
- 3) Microsoft Windows Server 2012 and 2012 R2 requires a hotfix. See Microsoft KB article 2833738.
- 4) Small Business Edition backup wizard does not allow the user to select the RDX or any other removable drive as the backup target. See Microsoft KB article 925097.
- 5) SLES 9 Service Pack 3 does not support SATA ATAPI devices and therefore does not support the RDX Internal SATA device.
- 6) Change RDX device operation mode to "fixed disk mode" for Windows Backup
- 7) Service Pack 4 (11.1.4) for System Recovery 2013 R2 needs to be installed in order to support Windows 10

RDX QuikStor Compatibility Matrix

EFFECTIVE: April 2016



Operating System Compatibility

RDX products are compatible with the following operating systems:

Operating System	Version	Notes
Windows XP Pro	All editions (32-bit & 64-bit)	1
Windows Vista	All editions (32-bit & 64-bit)	1
Windows 7	All editions (32-bit & 64-bit)	1, 2
Windows 8	All editions (32-bit & 64-bit)	1, 2, 5
Windows 8.1	All editions (32-bit & 64-bit)	1, 2
Windows 10	All editions (32-bit & 64-bit)	1, 2, 5
Windows 2003 (R2)	All editions (32-bit & 64-bit)	1, 4
Windows 2008 (R2)	All editions (32-bit & 64-bit)	1, 2, 5
Windows 2012 (R2)	All editions	1, 2
Small Business Server 2008		1, 2
Small Business Server 2011		1, 2
MacOS	OSX 10.4 (or later)	
Linux - RHEL	Ver 3.0, update 7 (or later)	
Linux - SUSE/OpenSUSE	Ver 9.0, service pack 3 (or later)	3
Linux - CentOS	Ver 4.2, Kernel version 2.6.9 (or later)	
Linux - Fedora Core 5	Kernel version 2.6 (or later)	
Linux - Ubuntu 12.04 or later		
AIX 5.3	5300-11 Technology Level or later	6
AIX 6.1	6100-04 Technology Level or later	6

Notes:

- 1) It is recommended to install RDX utility for full RDX and Media eject functionality on MS Windows operating systems
- 2) To use Windows Backup, please reconfigure your RDX drive in "Fixed disk mode" by using rdx utilities
- 3) SLES 9 Service Pack 3 does not support SATA ATAPI devices and therefore does not support the RDX Internal SATA device.
- 4) Small Business Edition backup wizard does not allow the user to select the RDX or any other removable drive as the backup target. Workaround is listed in Microsoft KB article 925097 or use NT Backup.
- 5) There are limitations with the Windows Server Backup application
- 6) Hubs/port replicators are not supported for attach of the USB removable disk drive for backup/restore

File System Compatibility

In principle the RDX cartridge can be formatted for any file system. The following file systems have been tested by Tandberg Data:

File System	Operating System	Notes
FAT32	Windows XP Windows Server 2008 Windows Vista SP1 Windows Server 2003 (R2) Windows Server 2008 (R2)	* Max file size = 4GB * Windows does not allow user to reformat cartridge as FAT32 * Windows Explorer may not display volume label the first time a cartridge is inserted
NTFS	Windows XP (Pro) Windows Vista SP1 Windows 7 Windows 8 Windows 10 Windows Server 2003 (R2) Windows Server 2008 (R2) Windows Server 2012 (R2)	
exFAT	Windows 7 Windows 8 Windows 10 Windows Server 2003 (R2) Windows Server 2008 (R2) Windows Server 2012 (R2)	
ext2/3/4	Linux	
XFS	Linux	
Mac OS Extended	Mac OS HPFS	

Limitations & Partition Format Scheme on Cartridges >2,2 TB

3TB RDX Cartridge Media must use GPT partition scheme to provide full capacity.

Operating System	Version	GPT Support	Notes
------------------	---------	-------------	-------

Notes:

RDX QuikStor Compatibility Matrix

EFFECTIVE: April 2016



Windows XP	32-bit	Not Supported	
Windows XP	64-bit	Limited Support	1
Windows 2003 w/o SP1	32-bit	Not Supported	
Windows 2003 with SP1	32-bit	Limited Support	1
Windows 2003 with SP1	64-bit	Limited Support	1

1) Partition layout cannot be changed

USB Compatibility

RDX USB drives should work with all USB controllers. Tandberg Data has tested the RDX USB drives with the USB controllers listed below:

Host Controller Types	Notes
EHCI (2.0) Enhanced Host Controller Interface	
UHCI (1.1) Universal Host Controller Interface	
OHCI (1.1) Open Host Controller Interface	

Notes:

- 1) The RDX USB drive is compatible with the USB Mass Storage specification for Bootability 1.0.
- 2) The USB RDX drives are certified to meet the USB-IF High Speed Compliance Standards for USB2.0 and USB3.0.
- 3) The following USB 3.0 PCIe HBAs are certified (NEC / Renesas Chipset): Akasa AK-PCCK 3-02, DeLock 89243 PCIe & StarTech PEXUSB3S11

Eject Button Support

Windows

Windows does not have native support for removable disk drives. Specifically, the operating system does not allow the eject button to operate with cartridges formatted with the NTFS file system. It does allow the user to eject the cartridge using Windows Explorer (right-click on drive letter, select "Eject").

Tandberg Data supplies a utility that allows the eject button to operate properly on Windows. This utility runs as a Windows service. See the RDX Utility Users Guide for installation instructions.

Linux/Mac OS X/Solaris

Linux, Solaris and Mac OS X do not typically support the eject button operation. Use the recommended system method to eject the removable media.

RDX QuikStation Compatibility Matrix

EFFECTIVE: April 2016



Operating System Compatibility

RDX products and RDX QuikStation are compatible with the following operating systems:

Operating System	Version	Notes
Windows XP Pro	All editions (32-bit & 64-bit)	
Windows Vista	All editions (32-bit & 64-bit)	
Windows 7	All editions (32-bit & 64-bit)	
Windows 8	All editions (32-bit & 64-bit)	2
Windows 8.1	All editions (32-bit & 64-bit)	2
Windows 10	All editions (32-bit & 64-bit)	2
Windows 2003 (R2)	All editions (32-bit & 64-bit)	1
Windows 2008 (R2)	All editions (32-bit & 64-bit)	2
Windows 2012 (R2)	All editions	
Small Business Server 2008		
Small Business Server 2011		
MacOS	MacOS X 10.7.5 (or later)	3,4
Linux - RHEL	Ver 3.0, update 7 (or later)	
Linux - SUSE/OpenSUSE	Ver 9.0, userservice pack 3 (or later)	
Linux - CentOS	Ver 4.2, Kernel version 2.6.9 (or later)	
Linux - Fedora Core 5	Kernel version 2.6 (or later)	
Linux - Ubuntu 12.04 or later		

Notes:

- 1) Small Business Edition backup wizard does not allow the user to select the RDX or any other removable drive as the backup target. Workaround is listed in Microsoft KB article 925097 or use NT Backup.
- 2) There are limitations with the native backup application.
- 3) MacOS X does not have native support for iSCSI devices. A third party iSCSI-Initiator software is necessary to establish a connection to the RDX QuikStation.
- 4) Connection tests performed using attotech Xtend SAN v3.45

File System Compatibility

In principle the RDX cartridge can be formatted for any file system. The following file systems have been tested by Tandberg Data:

File System	Operating System	Notes
FAT32	Windows XP Windows Server 2008 Windows Vista SP1 Windows Server 2003 (R2) Windows Server 2008 (R2)	* Max file size = 4GB * Windows does not allow user to reformat cartridge as FAT32 * Windows Explorer may not display volume label the first time a cartridge is inserted
NTFS	Windows XP (Pro) Windows Vista SP1 Windows 7 Windows 8 Windows 10 Windows Server 2003 (R2) Windows Server 2008 (R2) Windows Server 2012 (R2)	
exFAT	Windows 7 Windows 8 Windows 10 Windows Server 2003 (R2) Windows Server 2008 (R2) Windows Server 2012 (R2)	
ext2/3/4	Linux	
XFS	Linux	
Mac OS Extended	Mac OS HPFS	

Limitations & Partition Format Scheme on Cartridges >2,2 TB

3TB RDX Cartridge Media must use GPT partition scheme to provide full capacity.

Operating System	Version	GPT Support	Notes
Windows XP	32-bit	Not Supported	
Windows XP	64-bit	Limited Support	1

Notes:

- 1) Partition layout cannot be changed

RDX QuikStation Compatibility Matrix

EFFECTIVE: April 2016



Windows 2003 w/o SP1	32-bit	Not Supported	
Windows 2003 with SP1	32-bit	Limited Support	1
Windows 2003 with SP1	64-bit	Limited Support	1

Emulation Modes

RDX Product and RDX QuikStation can emulate the following devices:

Emulation Type	Logical Device
native RDX	Eight TD RDX Drives
Removable Disk	Eight removable disk devices
Tape Drives	Eight LTO-3 drives
Disk Autoloader	One RDX Drive & 8 Slots
TD StorageLibrary T24	Two LTO-3 drives and eight slots
TD StorageLoader LTO	One LTO-3 drive and eight slots
TD StorageLibrary T40+	Four LTO-3 drives and eight slots
Tape Autoloader	One LTO-3 drive and eight slots
Hybrid TD StorageLibrary T24 & RDX	Two LTO-3 drives and four slots and four TD RDX targets
Hybrid TD StorageLoader LTO & RDX	One LTO-3 drive and four slots and four TD RDX targets

Software Compatibility

Please check the corresponding section for the appropriate Device Emulation Type

Emulation Type	Software section to be checked	Notes
native RDX	Software Compatibility Matrix RDX	1
Removable Disk	See your Operating Systems HCL	
Eight Drives	Software Compatibility Matrix Tape Drives	
Disk Autoloader	N/A	
TD StorageLibrary T24	Software Compatibility Matrix Tape Automation	
TD StorageLoader LTO	Software Compatibility Matrix Tape Automation	
TD StorageLibrary T40+	Software Compatibility Matrix Tape Automation	
Tape Autoloader	Software Compatibility Matrix Tape Automation	
Hybrid TD StorageLibrary T24 & RDX	Software Compatibility Matrix Tape Automation & RDX	
Hybrid TD StorageLoader LTO & RDX	Software Compatibility Matrix Tape Automation & RDX	

Notes:

1) On the native RDX Mode is also a fixed disk mode available, which is recommended to be used with Windows Server Backup.

Eject Button Support

Windows

Windows does not have native support for removable disk drives. Specifically, the operating system does not allow the eject button to operate with cartridges formatted with the NTFS file system. It does allow the user to eject the cartridge using Windows Explorer (right-click on drive letter, select "Eject").

Tandberg Data supplies a utility that allows the eject button to operate properly on Windows. This utility runs as a Windows service. See the RDX Utility Users Guide for installation instructions.

Linux/Mac OS X/Solaris

Linux, Solaris and Mac OS X do not typically support the eject button operation. Use the recommended system method to eject the removable media.

RDX QuikStation 4 Compatibility Matrix

EFFECTIVE: April 2016



Operating System Compatibility

RDX products and RDX QuikStation 4 are compatible with the following operating systems:

Operating System	Version	Notes
Windows XP Pro	All editions (32-bit & 64-bit)	
Windows Vista	All editions (32-bit & 64-bit)	
Windows 7	All editions (32-bit & 64-bit)	
Windows 8	All editions (32-bit & 64-bit)	2
Windows 8.1	All editions (32-bit & 64-bit)	2
Windows 10	All editions (32-bit & 64-bit)	2
Windows 2003 (R2)	All editions (32-bit & 64-bit)	1
Windows 2008 (R2)	All editions (32-bit & 64-bit)	2
Windows 2012 (R2)	All editions	
Small Business Server 2008		
Small Business Server 2011		
MacOS	MacOS X 10.7.5 (or later)	3,4
Linux - RHEL	Ver 3.0, update 7 (or later)	
Linux - SUSE/OpenSUSE	Ver 9.0, service pack 3 (or later)	
Linux - CentOS	Ver 4.2, Kernel version 2.6.9 (or later)	
Linux - Fedora Core 5	Kernel version 2.6 (or later)	
Linux - Ubuntu 12.04 or later		

Notes:

- 1) Small Business Edition backup wizard does not allow the user to select the RDX or any other removable drive as the backup target. Workaround is listed in Microsoft KB article 925097 or use NT Backup.
- 2) There are limitations with the native backup application.
- 3) MacOS X does not have native support for iSCSI devices. A third party iSCSI-Initiator software is necessary to establish a connection to the RDX QuikStation.
- 4) Connection tests performed using attotech Xtend SAN v3.45

File System Compatibility

In principle the RDX cartridge can be formatted for any file system. The following file systems have been tested by Tandberg Data:

File System	Operating System	Notes
FAT32	Windows XP Windows Server 2008 Windows Vista SP1 Windows Server 2003 (R2) Windows Server 2008 (R2)	* Max file size = 4GB * Windows does not allow user to reformat cartridge as FAT32 * Windows Explorer may not display volume label the first time a cartridge is inserted
NTFS	Windows XP (Pro) Windows Vista SP1 Windows 7 Windows 8 Windows 10 Windows Server 2003 (R2) Windows Server 2008 (R2) Windows Server 2012 (R2)	
exFAT	Windows 7 Windows 8 Windows 10 Windows Server 2003 (R2) Windows Server 2008 (R2) Windows Server 2012 (R2)	
ext2/3/4	Linux	
XFS	Linux	
Mac OS Extended	Mac OS HPFS	

Limitations & Partition Format Scheme on Cartridges >2,2 TB

3TB RDX Cartridge Media must use GPT partition scheme to provide full capacity.

Operating System	Version	GPT Support	Notes
Windows XP	32-bit	Not Supported	
Windows XP	64-bit	Limited Support	1

Notes:

- 1) Partition layout cannot be changed

RDX QuikStation 4 Compatibility Matrix

EFFECTIVE: April 2016

Windows 2003 w/o SP1	32-bit	Not Supported	
Windows 2003 with SP1	32-bit	Limited Support	1
Windows 2003 with SP1	64-bit	Limited Support	1

Emulation Modes

RDX Product and RDX Quikstation 4 can emulate the following devices:

Emulation Type	Logical Device
native RDX	Eight TD RDX Drives
RDX Logical Volume	One Logical Volume

Software Compatibility

Please check the corresponding section for the appropriate Device Emulation Type

Emulation Type	Software section to be checked	Notes
native RDX	Software Compatibility Matrix RDX	1
RDX Logical Volume	See your Operating Systems HCL	

Notes:

1) On the native RDX Mode is also a fixed disk mode available, which is recommended to be used with Windows Server Backup.

Eject Button Support

Windows

Windows does not have native support for removable disk drives. Specifically, the operating system does not allow the eject button to operate with cartridges formatted with the NTFS file system. It does allow the user to eject the cartridge using Windows Explorer (right-click on drive letter, select "Eject").

Tandberg Data supplies a utility that allows the eject button to operate properly on Windows. This utility runs as a Windows service. See the RDX Utility Users Guide for installation instructions.

Linux/Mac OS X/Solaris

Linux, Solaris and Mac OS X do not typically support the eject button operation. Use the recommended system method to eject the removable media.