

Data Sheet

FUJITSU Server PRIMERGY RX1330 M2 Rack Server

Small in size and low in cost – rich in optional features

FUJITSU Server PRIMERGY will give you the servers you need to power any workload and changing business requirements. As business processes expand so does the need for applications. Each has its own resource footprint, so you need a way to optimize your computing to better serve your users. PRIMERGY systems will help you match your computing capabilities to your business priorities with our complete portfolio of expandable PRIMERGY tower servers for remote and branch offices, versatile rack-mount servers, compact and scalable blade systems, as well as hyper-converged scale-out servers. They convince by business proven quality with a wide range of innovations, highest efficiency cutting operational cost and complexity, provide more agility in daily operations, and integrate seamlessly to let help you concentrate on core business functions.

FUJITSU Server PRIMERGY RX rack systems are versatile rack-optimized servers providing best-in-class performance and energy efficiency, and thus form the “standard” in each data center. PRIMERGY RX servers deliver more than 20 years of development and production know-how resulting in extremely low failure rates below market average, and lead to continuous operations and outstanding hardware availability.

PRIMERGY RX1330 M2

The FUJITSU Server PRIMERGY RX1330 M2 is a mono-socket rack server designed to provide a solution for small budgets, yet enabling a rich set of optional expansions to best meet individual demands. Its usage patterns cover file, infrastructure and communication or collaboration applications by delivering up to 64 GB RAM, up to 3 PCIe slots and up to 10 2.5-inch hard disk drives. Moreover, this 1U server allows for diverse individual configurations with optional features, such as hot-plug power supply units, redundant fans and RAID controller. By delivering high

energy efficiency and operation in higher ambient temperature thanks to optional Cool-safe® Advanced Thermal Design, the PRIMERGY RX1330 M2 also contributes to very low operational costs. ServerView™ Suite and remote management features (iRMC S4) simplify the administration.



Features & Benefits

Main Features	Benefits
Low in costs ■ High energy efficient ■ Fujitsu ServerView™ suite and onboard remote management features (iRMC S4) enables centralized management ■ Cool-safe® Advanced Thermal Design enables operation in a higher ambient temperature Flexible foundation for infrastructure tasks ■ Intel Xeon processor E3-1200 v5 and up to 64 GB DDR4 memory, up to 3 PCIe slots and up to 10 storage drives ■ Free choice: Up to 4x 3.5-inch or up to 10x 2.5-inch storage drives ■ Broad selection of operating systems Rich set of optional features ■ Choice of Intel Xeon E3 v5, Core i3, Celeron and Pentium processors ■ Modular RAID controllers ■ Redundant fans ■ Hot-plug and redundant power supply (PSU) with 80 PLUS platinum energy efficiency (94 %) ■ Full-height PCIe slot Integrated UPS - Easy & reliable ■ The Fujitsu FJBU internal battery backup is an alternative for classical UPS devices ■ Compact battery unit that fits into modular PSU slot ■ Ni-MH battery allows for a very long life time (5 years) ■ Full integration into server management environment	■ Clear reduction in energy costs saving OPEX ■ Comprehensive and simplified management reduce time for standard administration tasks ■ Each additional degree means approximately 5-6 percent less energy costs for air-conditioning ■ Cost-optimized foundation for file, infrastructure and communication applications ■ Flexible to meet the individual demand, the huge storage capacity fulfills requirements of storage demanding application or services ■ Red Hat Linux, Suse Linux, Microsoft Windows Server - it's up to you ■ Perfectly meet the performance requirements with available budget ■ Match redundancy requirements with available budget ■ Keeps the server running during short blackouts or voltage fluctuations and enables a graceful shutdown ■ Same life time as the server – no maintenance necessary ■ Easy and clean setup: no cabling, no separate device

Technical details

PRIMERGY RX1330 M2

Base unit	RX1330 M2 LFF	RX1330 M2 LFF	RX1330 M2 SFF	RX1330 M2 SFF	RX1330 M2 SFF 10xSFF
Housing types	Rack	Rack	Rack	Rack	Rack
Storage drive architecture	3.5-inch SAS/SATA	3.5-inch SAS/SATA	2.5-inch SAS/SATA	2.5-inch SAS/SATA	2.5-inch SAS/SATA
Power supply	Standard	Hot-plug	Standard	Hot-plug	Hot-plug
Product Type	Mono Socket Rack Server	Mono Socket Rack Server	Mono Socket Rack Server	Mono Socket Rack Server	Mono Socket Rack Server

Mainboard

Mainboard type	D3375
Chipset	Intel® C236
Processor quantity and type	1 x Intel® Xeon® processor E3-1200 v5 product family / Intel® Core™ i3 processor / Intel® Pentium® processor / Intel® Celeron® processor

Processor	Intel® Celeron® processor G3900 (2C/2T, 2.80 GHz, TLC: 2 MB, Turbo: No, 2,133 MHz, 51 W)
	Intel® Core™ i3-6100 processor (2C/4T, 3.70 GHz, TLC: 3 MB, Turbo: No, 2,133 MHz, 51 W)
	Intel® Pentium® processor G4400 (2C/2T, 3.30 GHz, TLC: 3 MB, Turbo: No, 2,133 MHz, 54 W)
	Intel® Xeon® processor E3-1220v5 (4C/4T, 3.00 GHz, TLC: 8 MB, Turbo: 3.50 GHz, 2,133 MHz, 80 W)
	Intel® Xeon® processor E3-1225v5 (4C/4T, 3.30 GHz, TLC: 8 MB, Turbo: 3.70 GHz, 2,133 MHz, 80 W)
	Intel® Xeon® processor E3-1230v5 (4C/8T, 3.40 GHz, TLC: 8 MB, Turbo: 3.80 GHz, 2,133 MHz, 80 W)
	Intel® Xeon® processor E3-1240Lv5 (4C/8T, 2.10 GHz, TLC: 8 MB, Turbo: 3.20 GHz, 2,133 MHz, 25 W)
	Intel® Xeon® processor E3-1240v5 (4C/8T, 3.50 GHz, TLC: 8 MB, Turbo: 3.90 GHz, 2,133 MHz, 80 W)
	Intel® Xeon® processor E3-1260Lv5 (4C/8T, 2.90 GHz, TLC: 8 MB, Turbo: 3.90 GHz, 2,133 MHz, 45 W)
	Intel® Xeon® processor E3-1270v5 (4C/8T, 3.60 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,133 MHz, 80 W)
	Intel® Xeon® processor E3-1280v5 (4C/8T, 3.70 GHz, TLC: 8 MB, Turbo: 4.00 GHz, 2,133 MHz, 80 W)

Memory slots	4 (2 banks with 2 DIMMs each)
Memory slot type	DIMM (DDR4)
Memory capacity (min. - max.)	4 GB - 64 GB
Memory protection	ECC
Memory notes	Dual channel support. For dual channel performance, a minimum of 2 memory modules have to be ordered. Capacity per channel has to be the same.

Memory options	4 GB (1 module(s) 4 GB) DDR4, unbuffered, ECC, 2,133 MHz, PC4-2133, DIMM, 1Rx8
	8 GB (1 module(s) 8 GB) DDR4, unbuffered, ECC, 2,133 MHz, PC4-2133, DIMM, 2Rx8
	16 GB (1 module(s) 16 GB) DDR4, unbuffered, ECC, 2,133 MHz, PC4-2133, DIMM, 2Rx8

Interfaces

USB 3.0 ports	6 x (2x front, 4x rear) (10x 2.5" HDD base unit: 1x USB 2.0, 4x rear USB 3.0)
Graphics (15-pin)	1 x VGA (15-pin) / optional 1 x front VGA (not for 10x 2.5" HDD base unit)
Serial connection	1 x serial RS-232-C, usable for iRMC S4 or system or shared
LAN / Ethernet (RJ-45)	2 x 1 Gbit/s Ethernet
Management LAN (RJ45)	1 x dedicated management LAN port for iRMC S4 (10/100/1000 Mbit/s) Management LAN traffic can be switched to shared onboard Gbit LAN port

Onboard or integrated Controller

RAID controller	Integrated RAID 0/1 or RAID 5/6 controller (option) All hardware storage controller options are described under Components
SATA Controller	Intel® C236, 1 port used for accessible drive or SATA DOM 4 port for internal SATA HDDs with RAID 0, 1, 10 for Windows and Linux;
LAN Controller	Intel® i210 onboard. 2 x 10/100/1000 Mbit/s Ethernet (TCP/IP acceleration). iSCSI, PXE-Boot and WoL are supported
Remote management controller	Integrated Remote Management Controller (iRMC S4, 256 MB attached memory incl. graphics controller) IPMI 2.0 compatible
Trusted Platform Module (TPM)	Infineon / TPM 1.2 or TPM 2.0 module; TCG compliant (option)

Onboard or integrated Controller (Base unit specific)

RAID controller	4 port SATA with RAID 0/1/10 for HDDs	4 port SATA with RAID 0/1/10 for HDDs
SATA Controller	4-port SATA 6Gb with RAID 0, 1, 10	4-port SATA 3GB with RAID 0, 1, 10
SATA controller type notes	for hot-plug SATA hard disks	for hot-plug SATA hard disks

Slots

PCI-Express 3.0 x8	2 x Low profile Length 175mm; PCIe slot#1 = dedicated Modular RAID slot
PCI-Express 2.0 x4 (mech. x8)	1 x Low profile
Slot Notes	Optional support of 1x full height PCIe Gen3 x8 card, instead of 1x PCIe Gen2 x4 and 1x PCIe Gen3 x8

Drive bays

Storage drive bays	4/8 x 2.5-inch hot-plug SAS/SATA or 4x 3.5-inch hot-plug SAS/SATA or 10 x 2.5-inch hot-plug SAS/SATA
Accessible drive bays	1 x 5.25/0.4-inch for CD-RW/DVD
Notes accessible drives	Following limitations applies to 10x 2.5-inch HDD base unit: No CD-RW/DVD, 1x USB 2.0 at the front, no front VGA

Drive bays (Base unit specific)

Storage drive bays	Max. 4x 3.5-inch	Max. 8x 2.5-inch	Max. 10x 2.5-inch
--------------------	------------------	------------------	-------------------

Fan Configuration

Number of fans	4			
Fan notes	4 fans in combination with standard power supply or 5 fans in combination with hot-plug PSU base unit for 1+4 redundancy.			
Number of fans	4	5	4	5
Fan configuration	4 standard fan	5 redundant fan	4 standard fan	5 redundant fan
Fan notes	non redundant / non hot-plug	redundant / non hot-plug	non redundant / non hot-plug	redundant / non hot-plug

Operating panel

Operating buttons	On/off switch NMI button Reset button
Status LEDs	System status (orange) Identification (blue) Hard disks access (green) Power (green) At system rear side: System status (orange) Identification (blue) LAN connection (green) LAN speed (green / yellow)

BIOS

BIOS features	ROM based setup utility Recovery BIOS BIOS settings save and restore Local BIOS update from USB device Online update tools for main Windows and Linux versions Local and remote update via ServerView Update Manager Remote PXE boot support Remote iSCSI boot support
---------------	---

Operating Systems and Virtualization Software

Certified or supported operating systems and virtualization software	Microsoft® Hyper-V Server 2012 R2
	Microsoft® Windows Server® 2012 R2 Datacenter
	Microsoft® Windows Server® 2012 R2 Standard
	Microsoft® Windows Server® 2012 R2 Essentials
	Microsoft® Windows Server® 2012 R2 Foundation
	Microsoft® Windows Storage Server 2012 R2 Standard
	Microsoft® Hyper-V Server 2012
	Microsoft® Windows Server® 2012 Datacenter
	Microsoft® Windows Server® 2012 Standard
	Microsoft® Windows Server® 2012 Essentials
	Microsoft® Windows Server® 2012 Foundation
	Microsoft® Windows Storage Server 2012 Standard
	Microsoft® Hyper-V™ Server 2008 R2
	Microsoft® Windows Server® 2008 R2 Datacenter
	Microsoft® Windows Server® 2008 R2 Enterprise
	Microsoft® Windows Server® 2008 R2 Standard
	Microsoft® Windows Server® 2008 R2 Foundation
	VMware vSphere™ 6.0
	VMware vSphere™ 5.5
	SUSE® Linux Enterprise Server 12
	SUSE® Linux Enterprise Server 11
	Red Hat® Enterprise Linux 7
	Red Hat® Enterprise Linux 6
Operating system release link	http://docs.ts.fujitsu.com/dl.aspx?id=d4ebd846-aa0c-478b-8f58-4cfbf3230473
Operating system notes	VMware ESX hints: - SATA RAID is not supported - Storing virtual machines locally requires a SAS RAID Controller Support of other Linux derivatives on demand Red Hat® certification starting with version 5.8 / 6.4. Hardware requirements of Software Defined Storage supported by i.e. Microsoft Storage Spaces or VMWare vSAN please see Systemarchitect or paper configurator or datasheet of PSAS CP400i.

Server Management

Standard	ServerView Suite - Deploy
	Installation Manager
	Scripting Toolkit
	ServerView Suite - Control
	Operations Manager incl. PDA and ASR & R (Prefailure and Analysis; Automatic Server Recovery and Restart)
	Agents and CIM Providers / Agentless Service
	System Monitor
	RAID Manager
	Capacity Management
	Power Management
	Storage Support
	ServerView Suite - Maintain
	Remote Management (iRMC)
	Update Management (BIOS, Firmware, Windows Drives and SV Agents)
	Performance Measurement
	Asset Management
	Online Diagnostics
	ServerView Suite - Integrate
	Integration packs for Microsoft System Center, VMware vCenter, VMware vRealize, Nagios, and HP SIM
	Deployment tools and others

Server Management

Option	ServerView embedded Lifecycle Management Enhanced management functionalities for simplified, highly integrated and automated management processes ServerView Suite - Maintain iRMC Advanced Pack incl. Advanced Video Redirection (AVR), video capturing and Virtual Media ServerView Suite - Dynamize Virtual-IO Manager (VIOM)
Server Management notes	Regarding dependencies for ServerView Suite software products see dedicated product data sheets.

Dimensions / Weight

Rack (W x D x H)	482.6 mm (Bezel) / 435.4 mm (Body) x 572 x 42.8 mm
Height Unit Rack	1 U
Mounting Cable depth rack	200 mm cable depth
Weight	up to 13 kg
Weight notes	Actual weight may vary depending on configuration
Rack integration kit	Rack integration kit as option

Environment

Operating ambient temperature	5 - 40 °C (41 - 104 °F)
Operating temperature note	Cool-safe® Advanced Thermal Design (above 35 °C or below 10 °C) depending on configuration. For detailed information see relevant system configurator.
Operating relative humidity	10 - 85 % (non condensing)
Operating environment	FTS 04230 – Guideline for Data Center (installation specification)
Operating environment link	http://docs.ts.fujitsu.com/dl.aspx?id=e4813edf-4a27-461a-8184-983092c12dbe
Sound pressure (LpAm)	25 / 35 dB(A) (min / max idle), 25 / 35 dB(A) (min / max operating)
Sound power (LWAd; 1B = 10dB)	4.1 / 5.1 B (min / max idle), 4.1 / 5.1 B (min / max operating)
Noise notes	Noise emissions and operation modes depend on system configuration.

Electrical values

Power supply configuration	1x standard power supply or 1x hot-plug power supply or 2x hot plug power supplies for redundancy depending on model
Hot-plug power supply redundancy	Optional
Active power (max. configuration)	152 W
Apparent power (max. configuration)	155 VA
Heat emission (max. configuration)	547.2 kJ/h (518.6 BTU/h)
Rated current max.	4.0 A (100 V) / 2.0 A (240 V)
Active power note	To estimate the power consumption of different configurations use the Power Calculator of the System Architect: http://configurator.ts.fujitsu.com/public/
Power supply	300W standard, 92% (Gold efficiency), 100-240V, 50 / 60Hz 450W hot-plug, 94% (Platinum efficiency), 100-240V, 50 / 60Hz
Power supply notes	Power Safeguard adapts system performance in case the power requirements exceeds supply limits.
Battery backup	Fujitsu Battery Unit 380W, 12V (as option)

Compliance

Global	CB RoHS (Substance limitations in accordance with global RoHS regulations) WEEE (Waste electrical and electronic equipment)
Germany	GS
Europe	CE
USA/Canada	CSAc/us ULc/us FCC Class A
Japan	VCCI:V3 Class A + JIS 61000-3-2
Russia	GOST
South Korea	KC
China	CCC
Australia/New Zealand	C-Tick
Taiwan	BSMI

Compliance

Compliance link	http://globalsp.ts.fujitsu.com/sites/certificates
Compliance notes	There is general compliance with the safety requirements of all European countries and North America. National approvals required in order to satisfy statutory regulations or for other reasons can be applied for on request. * Warning: This is a class A product. In a domestic environment this product may cause radio interference in which case the user may be required to take adequate measures.

Components

Optical drives

Blu-ray Disc™ Triple Writer, (6x BD-RW, 8x DVD, 24x CD), ultraslim, SATA I
 DVD Super Multi ultra slim , (8x DVD; 24x CD), ultraslim, SATA I

Hard disk drives

HDD SATA, 6 Gb/s, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
 HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
 HDD SATA, 6 Gb/s, 500 GB, 7,200 rpm, 512e, hot-plug, 3.5-inch, economic
 HDD SATA, 6 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 4 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 2 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
 HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 3.5-inch, business critical
 HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512n, hot-plug, 2.5-inch, business critical
 HDD SATA, 6 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
 HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 900 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
 HDD SAS, 12 Gb/s, 600 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
 HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 600 GB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
 HDD SAS, 12 Gb/s, 450 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, hot-plug, 3.5-inch, enterprise
 HDD SAS, 12 Gb/s, 300 GB, 15,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
 HDD SAS, 12 Gb/s, 300 GB, 10,000 rpm, 512n, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 6 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
 HDD SAS, 12 Gb/s, 4 TB, 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
 HDD SAS, 12 Gb/s, 2 TB , 7,200 rpm, 512e, hot-plug, 3.5-inch, business critical
 HDD SAS, 12 Gb/s, 2 TB , 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
 HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 3.5-inch, enterprise
 HDD SAS, 12 Gb/s, 1.8 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512n, hot-plug, 3.5-inch, enterprise
 HDD SAS, 12 Gb/s, 1.2 TB, 10,000 rpm, 512e, hot-plug, 2.5-inch, enterprise
 HDD SAS, 12 Gb/s, 1 TB, 7,200 rpm, 512e, hot-plug, 2.5-inch, business critical
 HDD SAS, 6 Gb/s, 146 GB, 15,000 rpm, hot-plug, 2.5-inch, enterprise

Solid-State-Drive	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 960 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 800 GB, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 480 GB, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 400 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 400 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 400 GB, Mainstream Endurance, hot-plug, 2.5-inch, enterprise
	SSD SATA, 6 Gb/s, 240 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 240 GB, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 200 GB, Write-Intensive, hot-plug, 3.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 200 GB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 200 GB, Mainstream Endurance, hot-plug, 2.5-inch, enterprise
	SSD SATA, 6 Gb/s, 120 GB, Read-Intensive Endurance, hot-plug, 3.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 120 GB, Read-Intensive Endurance, hot-plug, 2.5-inch, enterprise, 0.3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 120 GB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 120 GB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 3.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.92 TB, Mixed-use, hot-plug, 2.5-inch, enterprise, 3 DWPD (drive writes per day for 5 years)
	SSD SATA, 6 Gb/s, 1.2 TB, Write-Intensive, hot-plug, 2.5-inch, enterprise, 10 DWPD (drive writes per day for 5 years)
SCSI / SAS Controller	DOM SATA, 6 Gb/s, 128 GB, non hot plug, enterprise, 345TBW (Seq. write)
	DOM SATA, 6 Gb/s, 64 GB, non hot plug, enterprise, 172TBW (Seq. write)
RAID Controller	LSI PSAS CP400e SAS Ctrl. 12 Gbit/s 8 ports ext. PCIe 3.0 x8
RAID Controller	Fujitsu PRAID EP420i for SafeStore, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP420i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 2 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID EP400i, RAID 5/6 Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 10, 5, 50, 6, 60, 1 GB, Optional FBU based on LSI SAS3108
	Fujitsu PRAID CP400i, RAID Ctrl., SAS/SATA 12 Gbit/s, 8 ports int. RAID level: 0, 1, 1E, 10, 5, 50, No FBU support
Fibre Channel controller	Fibre Channel Host Bus Adapter 1 x 8 Gbit/s QLogic QLE2560 MMF LC-style
	Fibre Channel Host Bus Adapter 2 x 8 Gbit/s QLogic QLE2562 MMF LC-style
	Fibre Channel Host Bus Adapter 1 x 8 Gbit/s Emulex LPe1250 MMF LC-style
	Fibre Channel Host Bus Adapter 2 x 8 Gbit/s Emulex LPe12002 MMF LC-style
Communication, Network	Ethernet Ctrl. 1 x 1 Gbit/s PCIe 2.1 x1 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 2.0 x8 SFP+ (Fujitsu)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 2.1 x8 RJ45 (Intel®)
	Ethernet Ctrl. 2 x 10 Gbit/s PCIe 3.0 x8 SFP+ (Emulex)
	Ethernet Ctrl. 2 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)
	Ethernet Ctrl. 4 x 1 Gbit/s PCIe 2.1 x4 RJ45 (Intel®)

Graphics add on cards	NVIDIA® NVS™315 LP, PCIe x16, 2x DVI/VGA
Rack infrastructure	Rackmount kit full extraction (665mm), tool less mounting, length variable 559-914mm Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm Rackmount kit full extraction (815mm), tool less mounting, length variable 559-914mm Rackmount kit tool less mounting Cable Management 1U for PRIMECENTER- and 3rd-party racks
Warranty	
Warranty period	1 year
Warranty type	Onsite warranty
Warranty Terms & Conditions	www.fujitsu.com/support
Product Support Services - the perfect extension	
Support Pack Options	Globally available in major business areas: 9x5, Next Business Day Onsite Response Time 9x5, 4h Onsite Response Time 24x7, 4h Onsite Response Time
Recommended Service	24x7 Onsite Service with 4h Onsite Response Time
Service Lifecycle	5 years after end of product life
Service Weblink	http://www.fujitsu.com/fts/products/product-support-services/

More information

Fujitsu OPTIMIZATION Services

In addition to Fujitsu PRIMERGY RX1330 M2, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Built on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offerings. This allows customers to select from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/products/computing/

Software

www.fujitsu.com/software/

More information

Learn more about Fujitsu PRIMERGY RX1330 M2, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.
<http://www.fujitsu.com/primergy>

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment>



Copyrights

All rights reserved, including intellectual property rights. Changes to technical data reserved. Delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see <http://www.fujitsu.com/fts/resources/navigation/terms-of-use.html>
©2016 Fujitsu Technology Solutions GmbH

Disclaimer

Technical data is subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.